


# CMIF/CP DA - Pneumatically actuated compact diaphragm valve DN 12:15

Pneumatically actuated diaphragm valve with metric plain socket ends for socket welding, Double Acting.



## EPDM

Reference	system	Category	family	series	d	DN	PN	R <sub>a</sub>	L	H	h	J	g
CMIFDA016E	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	16	12	6	G 1/4"	14	75	8	M5	360
CMIFDA020E	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	20	15	6	G 1/4"	16	75	8	M5	360

## FKM

Reference	system	Category	family	series	d	DN	PN	R <sub>a</sub>	L	H	h	J	g
CMIFDA016F	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	16	12	6	G 1/4"	14	75	8	M5	360
CMIFDA020F	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	20	15	6	G 1/4"	16	75	8	M5	360

## PTFE

Reference	system	Category	family	series	d	DN	PN	R <sub>a</sub>	L	H	h	J	g
CMIFDA016P	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	16	12	6	G 1/4"	14	75	8	M5	360
CMIFDA020P	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	20	15	6	G 1/4"	16	75	8	M5	360

# CMIF/CP DA – Pneumatically actuated compact diaphragm valve DN 12:15

The new compact and light piston actuator in PP-GR makes the CM/CP the ideal choice for applications requiring very frequent valve operation and a long valve lifetime.

- Compact and lightweight piston actuator in PP-GR, free of exposed metallic parts, particularly suited for use in severe environmental and chemically aggressive conditions.
- High strength IXEF piston guarantees high reliability over time without maintenance.
- High visibility graduated optical position indicator protected by a transparent cap with a seal O-Ring.
- The valve is impervious to fluids containing impurities
- It has an high flow rate
- It can be installed in any position
- It has an extremely compact structure
- It is actuated by a dry running piston and does not require maintenance
- It has no protruding screws and is fully free of impurity deposits
- Allows for an easy diaphragm seal replacement
- The Standard version valve comes with a position indicator.