


# CMFF/CP NO - Pneumatically actuated compact diaphragm valve DN 12:15

Pneumatically actuated diaphragm valve with BS parallel socket threaded ends, Normally Open.





### **EPDM**

Reference	system	Category	family	series	R	DN	PN	Ra	L	Н	h	J	g
CMFFNO038E	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	3/8"	12	6	G 1/4"	11.5	75	8	M5	360
CMFFNO012E	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	1/2"	15	6	G 1/4"	15	75	8	M5	360

### **FKM**

Reference	system	Category	family	series	R	DN	PN	Ra	L	Н	h	J	g
CMFFNO038F	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	3/8"	12	6	G 1/4"	11.5	75	8	M5	360
CMFFNO012F	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	1/2"	15	6	G 1/4"	15	75	8	M5	360

## PTFE

Reference	system	Category	family	series	R	DN	PN	Ra	L	Н	h	J	g
CMFFNO038P	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	3/8"	12	6	G 1/4"	11.5	75	8	M5	360
CMFFNO012P	Automation system	Pneumatically actuated valves	Diaphragm valves	CM/CP DN 12÷15	1/2"	15	6	G 1/4"	15	75	8	M5	360





## CMFF/CP NO - Pneumatically actuated compact diaphragm valve DN 12:15

The new compact and light piston actuator in PP-GR makes the CM/CP the ideal choice for applications requiring very frequent valve operation and a long valve lifetime.

- Compact and lightweight piston actuator in PP-GR, free of exposed metallic parts, particularly suited for use in severe environmental and chemically aggressive conditions.
- High strength IXEF piston guarantees high reliability over time without maintenance.
- · High visibility graduated optical position indicator protected by a transparent cap with a seal O-Ring.
- · The valve is impervious to fluids containing impurities
- · It has an high flow rate
- · It can be installed in any position
- · It has an extremely compact structure
- It is actuated by a dry running piston and does not require maintenance
- It has no protruding screws and is fully free of impurity deposits
- · Allows for an easy diaphragm seal replacement
- The Standard version valve comes with a position indicator.

